



ALLSTRIP

Universal NEP-FREE solvent used in ultrasonic processes to quickly eliminate glues, polishes, waxes, dyes and monomer residues.

COMPATIBILITY

- All metals, including galvanised metal
- Organic glass: CR39, TRIVEX...
- Mineral glass: Quartz, BK7, B270, Flat glass, KG2 filter, Germanium, Calcium Fluoride...

INGREDIENTS

- Does not contain halogenated products, NEP or modified alcohol

PHYSICAL AND CHEMICAL DATA

- pH concentrated: n.m.
- Density: 0.990
- Flash Point: 88°C

INSTRUCTIONS FOR USE

- Concentration: 100%
- Temperature: 20 to 50°C (68 to 122°F)


Bath temperature must be monitored and a cooling system added if temperature exceeds 50°C (122°F)

- Time: 2 to 10 minutes


Use in a space that is naturally ventilated or equipped with an aspiration system. ALLSTRIP can be used without ultrasonic, in which case, parts should be kept in motion inside the bath.

PROCESS EXAMPLES

- Removes oils from all types of parts (efficient on blind holes)



- Removal of temporary protective Zapon varnish from brass or galvanic brass dials



If you have any questions, please contact our Application Centre on: +41 22 365 46 66

NGL CLEANING TECHNOLOGY SA - ECOLOGICAL CLEANING SOLUTIONS

Chemin de la Vuarpillière 7 // CH-1260 NYON // SWITZERLAND
+41 22 365 46 66 // contact@ngl-group.com // www.ngl-group.com



BENEFITS

- Does not contain NEP
- Eliminates all organic residues (glue, wax, varnish, etc)
- Emulsifies and dissolves grease
- Disperses contaminants
- Excellent alternative to acetone
- Can be distilled in vacuum chambers
- This product is not inflammable (flash point > 65°C)
- Item surface slightly water-repellent