



SCHUTZLACK ROSE SPRAY

Masking varnish for protection of surfaces during mechanical operations (machining or satin finishing) or thermal (laser engraving operations, welding).



JEWELLERY RANGE

FUNCTION	APPLICATION/POLLUTION
Protection lacquer	N.A.

COMPATIBILITY

- All metals

COMPONENTS

- Isopropanol, acetone
- Polymers, dye
- No CMR compound, REACH compliant

PHYSICOCHEMICAL DATA

- Aerosol 400 ml
- Not watersoluble
- Colour: pink
- Density: 0.8
- % sec: 5.3 - 6.0
- Flash point: <21°C

INSTRUCTIONS FOR USE

- Spray the surface which needs protection from a distance 10-20 cm
- Leave the lacquer to dry for 5-10 min. depending on the amount sprayed
- After use: turn the container and press the valve until only gas comes out
- Container is under pressure
- Do not spray against a flame or any source of ignition
- Do not pierce or burn even after use
- Do not smoke

PROCESS EXAMPLES

- Schutzlack removal from stainless steel


CLEANING

RODACLEAN 2018	TAP WATER RINSE	DI WATER RINSE	HOT AIR DRYING
Tap water Conc.: 3-5% Temp.: 40-70°C 104-158°F Time: 2-5 min	Temp.: 20-30°C 68-86°F Time: 3-5 min	Temp.: 20-30°C 68-86°F Time: 3-5 min	

- Schutzlack removal from copper alloys and sensitive steels

CLEANING

GALVEX 20.02	TAP WATER RINSE	DI WATER RINSE	HOT AIR DRYING
Tap water Conc.: 2-4% Temp.: 40-70°C 104-158°F Time: 3-5 min	Temp.: 20-30°C 68-86°F Time: 3-5 min	Temp.: 20-30°C 68-86°F Time: 3-5 min	



10/03/26

STORAGE CONDITIONS

- Protect from sunlight and do not expose to temperatures exceeding 50°C (122°F). Keep well away from all sources of ignition.
- The shelf life of the product is 24 months from the date of manufacture, under the appropriate storage conditions.



If you have any questions, please contact our Application Centre on: +41 22 365 46 66

NGL CLEANING TECHNOLOGY SA - PRECISION CLEANING SOLUTIONS

Chemin de la Vuarpillièrre 7 – CH-1260 NYON – SWITZERLAND
+41 22 365 46 66 – contact@ngl-group.com – www.ngl-group.com

SWISS QUALITY

